nanoHydra-AI-4HDTVI

Quad HDTVI input Al Video Inference Platform

The nanoHydra-AI-4HDTVI is part of AMP's nanoHydra-AI video appliance range that integrate powerful AI/ML processors with multi-spectral live video inputs. The nanoHydra-AI-4HDTVI uses an NVIDIA® JetsonTM Xavier NX processor and features quad HDTVI live video inputs for building vision-enabled AI applications. This rugged video appliance is ideal for rapid deployment in demanding applications in Military, Communications, Transportation and Energy industries.



The nanoHydra-AI-4HDTVI supports quad HDTVI inputs at up to 1080p30 or 4M25 for 2 channels. The inputs can be simultaneously captured for AI processing / Inference. The nanoHydra-AI-4HDTVI has in-unit NVMe storage and provides a gigabit Ethernet connection for control and data transfer as required by the application. Internal expansion is provided as PCIe/104 OneBank $^{\mathsf{TM}}$ or miniPCie allowing additional application specific hardware to be added to the system.

The nanoHydra-AI-4HDTVI has an integrated power supply and can be driven from a regulated 9-15V DC input. The system is housed in a rugged, watertight, conduction cooled, IP67 rated enclosure with sealed MIL-D38999 connectors and is ready to be installed into mobile platforms and harsh environments.

Key Features

- 4x HDTVI inputs:
 - 4x up to 1080p30
 - 2x up to 4M25
- 8x PAL/NTSC/RS-170 video channels (option)
- NVIDIA® Jetson[™] Xavier NX processor
- Highly customizable AI video inference system
- Gigabit Ethernet
- Integrated NVMe storage
- Rugged IP67 enclosure
- 9V to 15V Power Supply
- MIL-D38999 connectors for secure cabling

RVAP


The nanoHydra-AI is one of AMP's Ready Video Appliance Platforms (RVAP). Using proven rugged PC/104 modules with a custom designed IP67 enclosure, our RVAP are SWaP optimised COTS solutions for a wide range of embedded video requirements.


Contact us for details on how RVAP can help in your project.






Mechanical Drawing







Example Applications

The nanoHydra-AI-4HDTVI is a highly configurable AI video inference platform ready for rapid development and deployment of vision enabled AI video systems. The nanoHydra-AI-4HDTVI is ideal for applications such as:

- Remote operated vehicle
- Autonomous vessels
- Situational Awareness
- Accident prevention
- Worker Safety

- Reconnaissance
- Threat detection
- Infrastructure inspection
- Vehicle monitoring
- Automatic Number plate recognition (ANPR)

Advanced Micro Peripherals Ltd Cambridge, CB6 2HY, England Tel (+44) 1353 659500 Fax (+44) 1353 659600 sales@ampltd.com http://www.ampltd.com Advanced Micro Peripherals Inc New York, NY10007, USA Tel (+1) 212 951 7205 Fax (+1) 212 658 9073 sales@amp-usa.com http://www.amp-usa.com





Technical Specification

AI Processor Module

NVIDIA® Jetson Xavier™ NX AI Performance: 21TOPS

GPU: 384-core NVIDIA Volta™ GPU with 48 Tensor Cores

CPU: 6-core NVIDIA Carmel ARM® v8.2 64bit

Memory: 8GB 128-bitLPDDR4x Storage: 16GB eMMC 5.1

Analog Video Inputs

Quad HDTVI input

Up to 1080p30 for 4x channels Up to 4M25 for 2x channels

8x independent PAL/NTSC/RS-170 inputs (option)

Video Compression

ITU-T H.264 (ISO/IEC 14496-10) ITU-T H.265 (ISO/IEC 23008-2) Real-time multi stream video encode

Network Interface

1x Gigabit Ethernet Control, Data transfer, video streaming

Storage

Internal M.2 (Key M) NVMe SSD (factory fitted)

Expansion

PCIe/104 OneBank™ miniPCIe (PCIe104 to miniPCIe bridge card - option)

Power

9-15V regulated DC input

Mechanical

Milled from solid Aluminium Alloy block

Size: 160 x 120 x 69 mm (6.3 x 4.7 x 2.7 inch) LWH

MIL-D38999 Connectors

Environmental

Operating temp –40°C to +70°C IP67 dust-proof, water immersion to 1m

Software

Uses the NVIDIA JetPack ecosystem:
DeepStream, CUDA, TensorRT
Support for Ubuntu Linux
Board Support Package
Application notes:
Al Video analytics
Video encoding and streaming

Standards Compliance


MIL-STD-810G(1)

Ordering Information

nanoHydra-Al-4HDTVI

Quad HDTVI input AI video inference platform

Functional Diagram



(1) The AMP nanoHydra family is designed to meet MIL-STD-810G requirements. Individual configurations are qualified through similarity with a base nano-Hydra configuration.

Advanced Micro Peripherals Ltd Cambridge, CB6 2HY, England Tel (+44) 1353 659500 Fax (+44) 1353 659600 sales@ampltd.com http://www.ampltd.com Advanced Micro Peripherals Inc New York, NY10007, USA Tel (+1) 212 951 7205 Fax (+1) 212 658 9073 sales@amp-usa.com http://www.amp-usa.com

